

AIRSTOP SOLO

ADHESIVE TAPE



THE ADHESIVE TAPE WITHOUT LINER FOR FAST INSTALLATION



Liner-free



Easily torn off



Quickly applied



High adhesion

ISOCELL

ADVANTAGES

- A PATENTED SPECIAL FOIL
 - Easily torn off crosswise by hand
 - Lengthwise tear-resistant fibre inlay
- FINETUNING SPECIAL FOIL:
 - Smooth application
 - Very easy to use
- LINER-FREE
 - Faster application
 - Saves time and cost for disposal
- PERFECT ADHESION AND APPLICATION

PRODUCT DATA

Roll width	60 mm 100 mm
Roll length	50 m
Composition	special foil reinforcement fabric acrylic adhesive
Temperature resistance	-40 °C – +80 °C

FIELD OF APPLICATION

- Bonding of vapour retarders and barriers
- Adhesive for OSB and MDF indoors and out
- Joints and connections on wood, masonry and metal



No garbage



No collecting liners



HEALTHY LIVING
SOLVENT-FREE
INDOOR QUALITY TESTED




DIN 4108-11 INCL. AGING
DIN 4108-7
ÖNORM B 8110-2
SIA 180




○ AIRTIGHTNESS TO STANDARD

AIRSTOP SOLO

ADHESIVE TAPE



AIRSTOP SOLO ADHESIVE TAPE FOR USE INDOORS AND OUT



Promotes
healthy living



Smooth application



○ BLENDS WITH WOOD EFFECT




○ PRACTICAL APPLICATION


AIRSTOP SOLO

ADHESIVE TAPE

APPLICATION METHOD



Loose end (below) can be fixed with continuous AIRSTOP SOLO Adhesive Tape.



AIRSTOP SOLO Adhesive Tape can be continued ≥ 3 cm over the lower tape.



BONDING TECHNOLOGY

When affixing the adhesive tape its full surface must bond with the substrate. The higher the contact pressure, the better the adhesion (pressing roller). Care must be taken to attach the adhesive tape completely and without tension in corners. We recommend sealing compound AIRSTOP SPRINT for plastered surfaces or very rough wood. Materials used must be free from dust and grease and in addition the substrate must be dry and capable of bearing loads. In case of doubt we recommend pre-treatment of the substrate with ISOCELL Primer.

[Observe guidelines for use in Product Data Sheet!](#)

RECOMMENDED ACCESSORIES

AIRSTOP RAK Squeegee

Pressure aid for optimum handling — particularly in corners.



AIRSTOP ROLL Pressure Roller

For optimum pressure to acrylic adhesive tapes. Roller of 40 mm cellular rubber — in particular for uneven and rough substrates.



ISOCELL GmbH & Co KG

Gewerbestraße 9 | 5202 Neumarkt am Wallersee
Tel.: +43 6216 4108-0 | Fax: +43 6216 7979
E-Mail: office@isocell.at | WWW.ISOCELL.COM

ISOCELL